


Design 1997

### EASY 3-D VIEWER

This aluminium daylight handheld viewer is made for the slide format 41x101 mm. or 2x 50x50 mm. slides. The viewer is pre-set on one slide format. To change the slide format, you have to de-assemble the total viewer to turn the slide holder to the other slide format (that means no quick change of slide format as our "Combi viewer" does).



- The maximum picture size for slide frame 41x101 mm. is 24x33 mm.
  - For slide frame 2x50x50 mm. the maximum size is 24x36 mm. horizontal only
  - The viewer has coated achromatic lenses F= 59 mm. ? 23 mm. (enlargement: 4,2).
  - Sharpness is adjustable by screwing the lenses individually in the body.
  - By pulling the lenses by hand from left to right, a lens separation correction over 11 mm. is reachable.
  - Changing the slide frame format requires some handiness, the viewer was not intend for much changing. Most users of this viewer are using one frame format. But if you have to change it, do it like the description below;
- \* Unscrew the two bolts at the underside of the viewer but keep the viewer still closed.
  - \* Put the viewer down, with the top side upwards, on a flat surface.
  - \* Take the top side carefully away.
  - \* Remove the left and right side of the viewer body.
  - \* Take the black slide frame holder out of the bottom with some friction. (try not to bend the springs)
  - \* Turn the slide frame holder with it's front side to the backside of the viewer body and replace it in the bottom. (not upside down!)
  - \* Replace the left and right side of the viewer body. (take into account the position of the other parts of the viewer)
  - \* Close the viewer with the top side very accurately! and keep it together.
  - \* Assemble the viewer body with the two bolts

Now the slide frame format is changed, enjoy the viewing!